

# One pipe end cap for all applications.



## The separable pipe end cap 129 TB from OBO simplifies your work.

Previously a small fault often resulted in a lot of work: The mounting of missing or faulty pipe end caps on conduits used to be an unpopular and elaborate task. Not any more – with the separable pipe end cap. Open, clip on, press together – and done! Without any disassembly of the installation. Needless to say, the separable pipe end cap also facilitates initial installation.

## Separable pipe end cap

M



### Pipe end cap, separable, metric



Separable pipe end cap to slot onto metric conduits.

The separable pipe end cap can be used for repairs on existing installations according to regulations. It is not necessary to disconnect the cables, allowing quick mounting.

Type	Size	Dim.		Dim.		Colour	Pack. pcs.	Weight kg/100 pcs.	Item no.
		D1 mm	D2 mm	L1 mm	L2 mm				
129 TB M16	M16	20	10	30	3	lichtgrau	50	0,400	2047812
129 TB M20	M20	24	13,4	30	3	lichtgrau	50	0,440	2047831
129 TB M25	M25	30	18,4	30	3	lichtgrau	50	0,500	2047839
129 TB M32	M32	36	25,4	30	3	lichtgrau	50	0,656	2047855
129 TB M40	M40	44	33,4	30	3	lichtgrau	30	0,790	2047863
129 TB M50	M50	53	43	30	3	lichtgrau	30	0,935	2047890
129 TB M63	M63	67	56	30	3	lichtgrau	20	1,140	2047898

PE Polyethylene

M



### Pipe end cap, separable, metric



Separable pipe end cap to slot onto metric conduits.

The separable pipe end cap can be used for repairs on existing installations according to regulations. It is not necessary to disconnect the cables, allowing quick mounting.

Type	Size	Dim.		Dim.		Colour	Pack. pcs.	Weight kg/100 pcs.	Item no.
		D1 mm	D2 mm	L1 mm	L2 mm				
129 TB M16 SW	M16	20	10	30	3	schwarz	50	0,400	2047936
129 TB M20 SW	M20	24	13,4	30	3	schwarz	50	0,440	2047944
129 TB M25 SW	M25	30	18,4	30	3	schwarz	50	0,500	2047952
129 TB M32 SW	M32	36	25,4	30	3	schwarz	50	0,656	2047971
129 TB M40 SW	M40	44	33,4	30	3	schwarz	30	0,790	2047979
129 TB M50 SW	M50	53	43	30	3	schwarz	30	0,935	2047987
129 TB M63 SW	M63	67	56	30	3	schwarz	20	1,140	2047995

PE Polyethylene

Pg



### Pipe end cap, separable, PG



Separable pipe end cap to slot onto PG conduits.

The separable pipe end cap can be used for repairs on existing installations according to regulations. It is not necessary to disconnect the cables, allowing quick mounting.

Type	Size	Dim.		Dim.		Colour	Pack. pcs.	Weight kg/100 pcs.	Item no.
		D1 mm	D2 mm	L1 mm	L2 mm				
129 TB PG9	PG9	20	10	30	3	lichtgrau	50	0,400	2044509
129 TB PG11	PG11	24	12,5	30	3	lichtgrau	50	0,430	2044511
129 TB PG13,5	PG13,5	26	15	30	3	lichtgrau	50	0,460	2044513
129 TB PG16	PG16	28	16	30	3	lichtgrau	50	0,500	2044516
129 TB PG21	PG21	34	21,5	30	3	lichtgrau	50	0,590	2044521
129 TB PG29	PG29	38	30	30	3	lichtgrau	50	0,700	2044529
129 TB PG36	PG36	48	40,5	30	3	lichtgrau	30	0,870	2044536
129 TB PG42	PG42	60	47,5	30	3	lichtgrau	30	0,980	2044542
129 TB PG48	PG48	66	52	30	3	lichtgrau	20	1,060	2044548

PE Polyethylene

OBO Bettermann Holding GmbH & Co. KG  
P.O. Box 1120  
58694 Menden  
GERMANY

Customer Service  
Tel.: +49 23 73 89 - 17 00  
Fax: +49 23 73 89 - 12 38  
export@obo.de

www.obo-bettermann.com

**OBO**  
BETTERMANN